

7

Diagram 7 illustrates the assembly of the frame with the RP227 roller. The frame is shown with a grid of internal supports. A roller labeled "RP227" is being positioned at the bottom right corner. A label "Silicone PU/MS" with a 2° angle indicates the application of adhesive to the frame's edge. A 1° angle is also indicated near the roller.

8

1°

2°

Silicone PU/MS

COD. 0107.1M.001.XX

fiora COD. 0107.1M.001.XX
Instrucciones
Instructions
4

COD. 010907.IM.001.06

Sep-System

5
ANS
YEARS
ANS
ANNE
YÄHRE
JAAR

x1
SOP100-SOP150
SOP203-SOPV
SOPA80-SOPA100

x11/15/16
RP223

x11/15/16
RP225

x2
RP220

x1
RP227

x2
RP221

x1
SOP100-SOP150
SOP203-SOPV
SOPA80-SOPA100

x11/15/16
RP226

x22/30/32
RP222

x4
RP051

x4
RP035

x6
RP224

x1
RP229

x4
RP034



